



MILBANK[®]
ENERGY AT WORK

AP2300-03



Catalog Number	AP2300-03	Jaw Quantity	4 Terminal
Marketing Product Description	4 Terminal Ring Type 1 In Hub	Bypass Type	No Bypass
UPC	784572110830	Number of Meter Positions	1 Position
Length (IN)	2.25	Equipment Ground	Triplex Ground
Width (IN)	6.625	Hub Opening	1 Inch Hub
Height (IN)	7.125	Line Side Wire Range	12 - 1 AWG
Brand Name	Milbank	Load Side Wire Range	12 - 1 AWG
Type	Ring Type Meter Socket	Number Of Receptacles	0
Application	Meter Socket		
Standard	Non UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	100 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	2.25L x 6.625W x 7.125H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead		
Terminal	Single Mechanical		
Insulation	Glass Polyester		
Mounting	Surface Mount		
Enclosure	Aluminum with Powder Coat Finish		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.