

# Eaton APJ6485

Catalog Number: APJ6485

Eaton Crouse-Hinds series Arktite APJ plug, 60A, 0.50-1.45",  
Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum,  
600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APJ plug	APJ6485  UPC 782274050201
Product Length/Depth	Product Height
8.5 in	3.75 in
Product Width	Product Weight
3.75 in	2.9 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

0.50-1.45"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APJ6485 3D drawing](#)

### Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APJ\)](#)

### Installation instructions

[IF 1229 - Arktite Plugs and Receptacles, Model M4, 30, 60, 100A](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - APJ6485](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)