



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B12V 12-10 Vinyl Butt Splice, *Nsi Industries*

| | |
|------------------|--|
| Catalog Number | B12V |
| Manufacturer | Nsi Industries |
| Description | 12-10 Awg Vinyl Insulated Butt Splice, 50/Pack |
| Weight per unit | 0.2720 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|---------------------|------------------|
| Material | Vinyl Insulation |
| Number of Terminals | 2 |
| Terminal Size | 1.024 Long |
| Voltage Rating | 300 V |
| Warranty | 1 YEAR |
| Wire Size | 12-10 AWG |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Descriptions

| | |
|------------------------|--|
| Description | 12-10 VINYL BUTT SPLICE, |
| extra long description | NSI B12-V 12-10 Vinyl Butt Splice, |
| Features | 12-10 AWG Vinyl Insulated Butt Splice, 50/Pack |
| Long Description | 12-10 AWG Vinyl Insulated Butt Splice, 50/Pack |
| Product Type | 12-10 Vinyl Butt Splice, 50 Per Pack |
| Special Features | Vinyl Insulated 12-10 AWG - 50 Pack |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381069764 |
| Manufacturers Part Number | B12-V |
| UPC | 662381069764 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Vinyl Insulated Butt Connectors |

Availability

| | |
|-------------|----|
| minimum qty | 50 |
|-------------|----|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.272 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------|
| Application | Wire Splicing |
| environmental conditions | 75 C |
| standard | cULus |