



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2075 Polytuff NM Tubing, 3/4", BK *Hubbell Wiring Devices*

Catalog Number	B2075
Manufacturer	Hubbell Wiring Devices
Description	Hubbell Wiring Device Kellems, Kellems Wire Management, Liquidtightsystem, Polytuff Non-Metallic tubing, 3/4", Black
Weight per unit	0.1330 (lbs/each)
Product Category	Liquid Tight Conduit

Features

pallet quantity	2000
Voltage Rating	300

Material, Color, and Finish

Color	Black
Finish	Ribbed

Dimensions and Weight

Length	1200
--------	------

Descriptions

Description	POLYTUFF NM TUBING, 3/4", BK
extra long description	HWDK B2075 POLYTUFF NM TUBING, 3/4"

Features
Liquidtight tubing is designed to house and permanently protect underground cable from moisture, grit, rodents and other environmental hazards that can damage the cable over time. The Kellems brands of liquidtight — PolyTuff® I conduit and PolyTuff® II tubing —feature non-metallic, PVC-based construction, avoiding the challenges of corrosion while providing high strength, superior flexibility and outstanding handleability. When compared to metals, they can be deployed in flexible directions, even accomoda

Long Description	Hubbell Wiring Device Kellems, Kellems Wire Management, LiquidtightSystem, POLYTUFF Non-MetallicTubing, 3/4", Black
------------------	---

Product Type	Polytuff NM Tubing, 3/4", BK
Special Features	Wet and Damp Locations

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585333229
Manufacturers Part Number	B2075
UPC	783585333229



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Stainless Steel EMT Conduit

Type PolyTuff® II Liquidtight Tubing

Trade Size

Trade Size 3/4

Packaging

Carton 100

Package 0

Weight Per each 0.133

Uses, Certifications, and Standards

Application UL1660

standard CSA Certified;UL Recognized