

Eaton BAB1060

Catalog Number: BAB1060

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 60A, 10 kAIC, 120/240V



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB1060
	UPC
	786679301609
Product Length/Depth	Product Height
3.7 in	4.6 in
Product Width	Product Weight
1.2 in	0.35 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

60 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB1060](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)