




BEAM CLAMP, 1/4" ROD 1, #10 ROD 2, 1/2" MAX FLANGE

CATALOG NUMBER

BC



CERTIFICATIONS



FEATURES

Easy installation to beam flanges


PRODUCT ATTRIBUTES

Material: Spring Steel
Finish: nVent CADDY Armour
Rod Size 1 (RS1): 1/4"
Rod Size 2 (RS2): 10"
Hole Size (HS): 7/16"
Flange Thickness (FT): 1/2" Max
Torque (TQ): 20 in-lb
Static Load (F): 100lb

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER