



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BD12 1STR Flexible Copper Braid

*Burndy LLC*

Catalog Number	BD12
Manufacturer	Burndy LLC
Description	Copper Braid, 12" Long, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/4" Stud Hole Spacing, 190 Amps Indoor, 225 Amps Outdoor.
Weight per unit	0.3400 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Material	Copper
----------	--------

### Descriptions

Description	1STR FLEXIBLE COPPER BRAID
extra long description	BUR BD12 BRAID 12 IN 2 HOLE
Long Description	Copper Braid, 12" Long, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/4" Stud Hole Spacing, 190 Amps Indoor, 225 Amps Outdoor.
Product Type	Mechanical
Special Features	Made of flat extra flexible, tinned, pure copper braid, with unplated, seamless, pure copper ferrules formed into a rectangular shape on each end.

### Manufacturer Information

Brand	BURNDY
GTIN	00781810806975
Manufacturers Part Number	BD12
UPC	781810806975

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	B, Flexible

### Packaging

Carton	1
Package	50
Weight Per each	0.34

### Uses, Certifications, and Standards

Application	Flexible copper braid jumpers designed to take up linear expansion and contraction
standard	UL467