

Eaton BD3030

Catalog Number: BD3030

Eaton BR thermal magnetic circuit breaker, Type BD 1-Inch CTL plug-on breaker, Includes rejection tab feature, 30-30 A, 10 kAIC, Single-pole, 120V, BD, #14-4 AWG Cu/Al, BD, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BD3030
	UPC
	786676369503

Product Length/Depth	Product Height
2.9 in	2.5 in

Product Width	Product Weight
1 in	0.35 lb

Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

defaultTaxonomyAttributeLabel

Type

Type BD 1-Inch CTL plug-on breaker

Special features

Includes rejection tab feature

Amperage Rating

(2) 30A

Voltage rating

120 V

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BD

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BD3030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)