

Eaton BKLGE600B

Catalog Number: BKLGE600B

MAIN BKR KIT 480V MAX 1 OR 3PH 600A LG BOTTOM MOUNTING



General specifications

Product Name	Catalog Number
Eaton Pow-R-Stock main breaker kit	BKLGE600B
UPC	Product Length/Depth
786687010760	5.5 in
Product Height	Product Width
12 in	5.5 in
Product Weight	Certifications
16 lb	UL Listed

defaultTaxonomyAttributeLabel

Type

Breaker Kit

Bus material

Copper

Bus Rating

600 A

Circuit breaker type

LG

Feed type

Bottom

Mounting

Bottom

Nominal frequency

50 Hz

Number Of Poles

Three-pole

Operating Temperature

40°C

Phase

Single-phase, three-phase

Short-circuit rating

35000 kA

Wire size

#4 AWG-350 kcmil

Application

Commercial construction

Indicators

Local

Number of conductors

1 per phase

Operator

Manual

Primary voltage

277Y/480 V

Series

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKLGE600B](#)

C

Voltage - max

600



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)