

# Class CC, Type M and Class G Fuse Blocks

## BC Series



### Specifications

**Description:** Class CC fuse blocks for use with Class CC fuses ( Bussmann LP-CC, KTK-R, and FNQ-R).

**Dimensions:** See Data Sheet 1105

**Poles:** 1 to 3

### Ratings:

Volts: — 600V  
Amps: — 1/0-30A  
SCCR:— 200kA RMS Sym.

**Agency Information:** CE, UL Listed (Guide IZLT, File E14853), CSA (Class 6225-01, File 47235)

**Flammability Rating:** UL 94V0

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2

### Catalog Numbers

| Screw   | Terminal Type             |                |                                  |         | Poles |
|---------|---------------------------|----------------|----------------------------------|---------|-------|
|         | Screw with Quick Connect* | Pressure Plate | Pressure Plate w/ Quick Connect* | Box Lug |       |
| BC6031S | BC6031SQ                  | BC6031P        | BC6031PQ                         | BC6031B | 1     |
| BC6032S | BC6032SQ                  | BC6032P        | BC6032PQ                         | BC6032B | 2     |
| BC6033S | BC6033SQ                  | BC6033P        | BC6033PQ                         | BC6033B | 3     |

Data Sheet: 1105

## BCCM Series

**Description:** 3-pole fuse block for use with (2) Class CC fuses and (1) 1/2" x 1 1/2" fuse

### Catalog Numbers

| Catalog Numbers | Terminal Type                   |
|-----------------|---------------------------------|
| BCCM6033SQ      | Screw with Quick-Connect*       |
| BCCM6033PQ      | Pressure Plate w/Quick-Connect* |

\*Quick-connect terminal rated for 20A max.

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

## BM Series Type M



### Specifications

**Description:** Supplementary fuse blocks for use with any 1/2" x 1 1/2" fuses (Bussmann KTK, PVM, FNQ, FNM, BAF, PV, and AGU).

**Dimensions:** See Data Sheet 1104

**Poles:** 1 to 3

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2

### Ratings:

Volts: — 600Vac/dc  
Amps: — 1/0-30A  
SCCR:— 10kA RMS Sym.

**Agency Information:** CE, UL Recognized (Guide IZLT2, File E14853), CSA (Class 6225-01, File 47235).

**Flammability Rating:** UL 94V0.

### Catalog Numbers

| Screw with Quick Connect* | Terminal Type                    |         |  | Poles |
|---------------------------|----------------------------------|---------|--|-------|
|                           | Pressure Plate w/ Quick Connect* | Box Lug |  |       |
| BM6031SQ                  | BM6031PQ                         | BM6031B |  | 1     |
| BM6032SQ                  | BM6032PQ                         | BM6032B |  | 2     |
| BM6033SQ                  | BM6033PQ                         | BM6033B |  | 3     |

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

Data Sheet: 1104

## BG & G Series



### Specifications

**Description:** Class G fuse blocks for use with Class G fuses (Bussmann SC).

**Dimensions:** See Data Sheet 1106

**Poles:** 1 to 3

### Ratings:

Volts: — 600Vac/dc (0-20A)  
— 480Vac/dc (25-60A)  
Amps: — 1-60A (See Catalog Numbers table)  
SCCR: — 100kA RMS Sym.

**Agency Information:** CE, UL Listed 35-60A (Guide IZLT, File E14853), UL Recognized 1-30A, (Guide IZLT2, File E14853), CSA (Class 6225-01, File 47235).

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2.

### Catalog Numbers

| Screw with Quick Connect* | Terminal Type                    |           |                          |   | Amps  | Poles |
|---------------------------|----------------------------------|-----------|--------------------------|---|-------|-------|
|                           | Pressure Plate w/ Quick Connect* | Box Lug   | Box Lug w/retaining clip |   |       |       |
| BG3011SQ                  | BG3011PQ                         | BG3011B   | —                        | — | 1     |       |
| BG3012SQ                  | BG3012PQ                         | BG3012B   | —                        | — | 1-15  |       |
| BG3013SQ                  | BG3013PQ                         | BG3013B   | —                        | — | 3     |       |
| BG3021SQ                  | BG3021PQ                         | BG3021B   | —                        | — | 1     |       |
| BG3022SQ                  | BG3022PQ                         | BG3022B   | —                        | — | 20    |       |
| BG3023SQ                  | BG3023PQ                         | BG3023B   | —                        | — | 3     |       |
| BG3031S                   | BG3031P                          | BG3031B   | —                        | — | 1     |       |
| BG3032S                   | BG3032P                          | BG3032B   | —                        | — | 25-30 |       |
| BG3033S                   | BG3033P                          | BG3033B   | —                        | — | 3     |       |
| —                         | —                                | —         | G30060-1CR               | — | 1     |       |
| —                         | —                                | —         | G30060-2CR               | — | 35-60 |       |
| —                         | —                                | G30060-3C | G30060-3CR               | — | 3     |       |

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

Data Sheet: 1106

# Class CC, Type M and Class G Fuse Blocks

## BC Series



### Specifications

**Description:** Class CC fuse blocks for use with Class CC fuses ( Bussmann LP-CC, KTK-R, and FNQ-R).

**Dimensions:** See Data Sheet 1105

**Poles:** 1 to 3

### Ratings:

Volts: — 600V  
Amps: — 1/0-30A  
SCCR:— 200kA RMS Sym.

**Agency Information:** CE, UL Listed (Guide IZLT, File E14853), CSA (Class 6225-01, File 47235)

**Flammability Rating:** UL 94V0

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2

### Catalog Numbers

| Screw   | Terminal Type             |                |                                  |         | Poles |
|---------|---------------------------|----------------|----------------------------------|---------|-------|
|         | Screw with Quick Connect* | Pressure Plate | Pressure Plate w/ Quick Connect* | Box Lug |       |
| BC6031S | BC6031SQ                  | BC6031P        | BC6031PQ                         | BC6031B | 1     |
| BC6032S | BC6032SQ                  | BC6032P        | BC6032PQ                         | BC6032B | 2     |
| BC6033S | BC6033SQ                  | BC6033P        | BC6033PQ                         | BC6033B | 3     |

Data Sheet: 1105

## BCCM Series

**Description:** 3-pole fuse block for use with (2) Class CC fuses and (1) 1/2" x 1 1/2" fuse

### Catalog Numbers

| Catalog Numbers | Terminal Type                   |
|-----------------|---------------------------------|
| BCCM6033SQ      | Screw with Quick-Connect*       |
| BCCM6033PQ      | Pressure Plate w/Quick-Connect* |

\*Quick-connect terminal rated for 20A max.

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

## BM Series Type M



### Specifications

**Description:** Supplementary fuse blocks for use with any 1/2" x 1 1/2" fuses (Bussmann KTK, PVM, FNQ, FNM, BAF, PV, and AGU).

**Dimensions:** See Data Sheet 1104

**Poles:** 1 to 3

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2

### Ratings:

Volts: — 600Vac/dc  
Amps: — 1/0-30A  
SCCR:— 10kA RMS Sym.

**Agency Information:** CE, UL Recognized (Guide IZLT2, File E14853), CSA (Class 6225-01, File 47235).

**Flammability Rating:** UL 94V0.

### Catalog Numbers

| Screw with Quick Connect* | Terminal Type                    |         |  | Poles |
|---------------------------|----------------------------------|---------|--|-------|
|                           | Pressure Plate w/ Quick Connect* | Box Lug |  |       |
| BM6031SQ                  | BM6031PQ                         | BM6031B |  | 1     |
| BM6032SQ                  | BM6032PQ                         | BM6032B |  | 2     |
| BM6033SQ                  | BM6033PQ                         | BM6033B |  | 3     |

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

Data Sheet: 1104

## BG & G Series



### Specifications

**Description:** Class G fuse blocks for use with Class G fuses (Bussmann SC).

**Dimensions:** See Data Sheet 1106

**Poles:** 1 to 3

### Ratings:

Volts: — 600Vac/dc (0-20A)  
— 480Vac/dc (25-60A)  
Amps: — 1-60A (See Catalog Numbers table)  
SCCR: — 100kA RMS Sym.

**Agency Information:** CE, UL Listed 35-60A (Guide IZLT, File E14853), UL Recognized 1-30A, (Guide IZLT2, File E14853), CSA (Class 6225-01, File 47235).

**DIN-Rail Adapters:** See page 413 for DRA-1 & DRA-2.

### Catalog Numbers

| Screw with Quick Connect* | Terminal Type                    |           |                          |       | Amps | Poles |
|---------------------------|----------------------------------|-----------|--------------------------|-------|------|-------|
|                           | Pressure Plate w/ Quick Connect* | Box Lug   | Box Lug w/retaining clip |       |      |       |
| BG3011SQ                  | BG3011PQ                         | BG3011B   | —                        | 1-15  | 1    |       |
| BG3012SQ                  | BG3012PQ                         | BG3012B   | —                        |       | 2    |       |
| BG3013SQ                  | BG3013PQ                         | BG3013B   | —                        |       | 3    |       |
| BG3021SQ                  | BG3021PQ                         | BG3021B   | —                        | 20    | 1    |       |
| BG3022SQ                  | BG3022PQ                         | BG3022B   | —                        |       | 2    |       |
| BG3023SQ                  | BG3023PQ                         | BG3023B   | —                        |       | 3    |       |
| BG3031S                   | BG3031P                          | BG3031B   | —                        | 25-30 | 1    |       |
| BG3032S                   | BG3032P                          | BG3032B   | —                        |       | 2    |       |
| BG3033S                   | BG3033P                          | BG3033B   | —                        |       | 3    |       |
| —                         | —                                | —         | G30060-1CR               | 35-60 | 1    |       |
| —                         | —                                | —         | G30060-2CR               |       | 2    |       |
| —                         | —                                | G30060-3C | G30060-3CR               |       | 3    |       |

### Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

Data Sheet: 1106