

# Eaton BQ220230

Catalog Number: BQ220230

Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 20 A, (1) Two-Pole 30 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters



## General specifications

### Product Name

Eaton BR thermal magnetic circuit breaker

### Catalog Number

BQ220230

### UPC

786676370806

### Product Length/Depth

3 in

### Product Height

3 in

### Product Width

2 in

### Product Weight

0.7 lb

### Compliances

Federal Specifications Classification W-C375

### Certifications

UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BQ 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(1) Two-Pole 20A, (1) Two-Pole 30A

### Voltage rating

120/240 V

### Trip Type

Independent

### Circuit breaker type

BQ

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BQ

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Four-pole

### Quantity

28

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Specifications and datasheets

Eaton Specification Sheet - BQ220230



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)