

# Eaton BQ230250

Catalog Number: BQ230250

Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 30 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BQ230250

<b>UPC</b>
786676371100

<b>Product Length/Depth</b>	<b>Product Height</b>
2.4 in	3.3 in

<b>Product Width</b>	<b>Product Weight</b>
3.5 in	2.35 lb

<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 489

### Catalog Notes

All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

## defaultTaxonomyAttributeLabel

### Type

Type BQ 1-Inch CTL plug-on circuit breaker

### Special features

Includes rejection tab feature

### Amperage Rating

(1) Two-Pole 30A, (1) Two-Pole 50A

### Voltage rating

120/240 V

### Trip Type

Independent

### Circuit breaker type

BQ

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BQ

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Four-pole

### Quantity

28

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Specifications and datasheets

Eaton Specification Sheet - BQ230250



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)