

Eaton BR1224B100R

Catalog Number: BR1224B100R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 24-pole, 24 circuits, 12 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, b2r box size



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR1224B100R
UPC	Product Length/Depth
786676443951	20.4 in
Product Height	Product Width
5.5 in	15.1 in
Product Weight	Warranty
22.6 lb	10 year
Certifications	
UL 67	
UL 50	

Product specifications

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Wire size

#4-1/0 AWG Cu/Al

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

B2R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Specifications and datasheets

Eaton Specification Sheet - BR1224B100R

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)