

Eaton BR1224L125V1

Catalog Number: BR1224L125V1

Eaton Eaton BR main lug loadcenter, Value pack, 125 A, B1, Aluminum, NEMA 1, Metallic, 10 kAIC, BR, Combination, NEMA 1, 24 Circuits, Twenty-four pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR1224L125V1
UPC	Product Length/Depth
782116909988	3.88 in
Product Height	Product Width
16.75 in	14.31 in
Product Weight	Warranty
15.6 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Includes four breakers

defaultTaxonomyAttributeLabel

Special features

Value pack

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

B1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR1224L125V1

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)