

# Eaton BR1224L400R

Catalog Number: BR1224L400R

Eaton BR main lug loadcenter, 400 A,42,Aluminum, NEMA 3R, Surface,NEMA 3R,42 Circuits,24-pole,12 Spaces,3-wire,Single-phase,Type BR 1-inch breakers,120/240V,(2) #3/0–400 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR1224L400R
<b>UPC</b>	<b>Product Length/Depth</b>
786685895420	6.38 in
<b>Product Height</b>	<b>Product Width</b>
38 in	16.31 in
<b>Product Weight</b>	<b>Warranty</b>
49 lb	10 year limited
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Main lug

### Amperage Rating

400 A

### Bus material

Aluminum

### Cover

Cover included

### Mounting

Surface

### Number of circuits

42

### Number of spaces

12

### Phase

Single-phase

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

### NEMA rating

NEMA 3R

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR1224L400R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)