



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR1224N125 12/24C 125A 1PH Convertible Loadcenter

Eaton Corp

Catalog Number	BR1224N125
Manufacturer	Eaton Corp
Description	BR Loadcenter, Convertible Main, No Feed-Thru Lugs, BREQS125 Hold-Down Screw, 125A, Single-Phase, 24 Circuits, 12 Spaces, 120/240V, Wire Size Depends Upon Main Breaker Kit or Main Lug Kit, Nema 1 Enclosure, B2 Box Size, Aluminum Bus
Weight per unit	20.0 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	125 VAC
Box Size	SPC250L
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX47.6250centimetre
interrupt rating	10 kAIC
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
Number of Circuits	24 VDC
number of spaces	51869
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	Determined by circuit breaker installed

### Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

### Dimensions and Weight

Size	B2
------	----

### Descriptions

Description	12/24C 125A 1PH CONVERTIBLE LOADCENTER
extra long description	ETN BR1224N125 BR style 1-inch load
Long Description	BR loadcenter, convertible main, no feed-thru lugs, BREQS125 hold-down screw, 125A, single-phase, 24 circuits, 12 spaces, 120/240V, wire size depends upon main breaker kit or main lug kit, NEMA 1 enclosure, b2 box size, aluminum bus
Product Type	BR Style 1-Inch Loadcenter
Special Features	No feed-thru lugs, includes BREQS125 hold-down screw



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton
GTIN	00786676447959
Manufacturers Part Number	BR1224N125
UPC	786676447959

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	CONVERTIBLE MAIN
unspsc code	39121101

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	20

## Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50