

Eaton BR125

Catalog Number: BR125

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 25 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, BR, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR125
	UPC
	786676362153
Product Length/Depth	Product Height
3.3 in	3.3 in
Product Width	Product Weight
1.6 in	2.05 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

25 A

Voltage rating

120/240 V

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR125](#)