

# Eaton BR2020

Catalog Number: BR2020

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Two-pole, 120V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters



## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                          | <b>Catalog Number</b> |
| Eaton BR thermal magnetic circuit breaker    | BR2020                |
|  | UPC                   |
|  | 786676370257          |
| <b>Product Length/Depth</b>                  | <b>Product Height</b> |
| 1 in   | 2.5 in                |
| <b>Product Width</b>                         | <b>Product Weight</b> |
| 2.9 in                                       | 0.35 lb               |
| <b>Compliances</b>                           | <b>Certifications</b> |
| Federal Specifications Classification W-C375 | UL 489                |

## defaultTaxonomyAttributeLabel

### Type

Type BR 1-Inch plug-on circuit breaker

### Amperage Rating

(2) 20A

### Voltage rating

120 V

### Trip Type

Common breaker trip

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Two-pole

### Quantity

28

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR2020](#)