

Specifications

Eaton BR2024B125

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 125A, single-phase, 24-pole, 24 circuits, 20 spaces, 120/240V, #4-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size

General specifications

| | |
|----------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BR2024B125 |
| UPC | 786676444453 |
| PRODUCT LENGTH/DEPTH | 3.88 in |
| PRODUCT HEIGHT | 16.75 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 24 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |

| Product specifications | |
|------------------------|-------------------------|
| SPECIAL FEATURES | No feed-thru lugs |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 125 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 24 |
| NUMBER OF SPACES | 20 |
| PHASE | Single-phase |
| WIRE SIZE | #4-2/0 AWG Cu/Al |
| MOUNTING | Combination |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | C1 |
| ENCLOSURE | NEMA 1 |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |

| Resources | |
|-------------------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BR2024B125 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications

Eaton BR2024B125

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 125A, single-phase, 24-pole, 24 circuits, 20 spaces, 120/240V, #4-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size

General specifications

| | |
|----------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BR2024B125 |
| UPC | 786676444453 |
| PRODUCT LENGTH/DEPTH | 3.88 in |
| PRODUCT HEIGHT | 16.75 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 24 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |

| Product specifications | |
|------------------------|-------------------------|
| SPECIAL FEATURES | No feed-thru lugs |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 125 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 24 |
| NUMBER OF SPACES | 20 |
| PHASE | Single-phase |
| WIRE SIZE | #4-2/0 AWG Cu/Al |
| MOUNTING | Combination |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | C1 |
| ENCLOSURE | NEMA 1 |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |

| Resources | |
|-------------------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BR2024B125 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

