

Eaton BR2024B125

Catalog Number: BR2024B125

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 125A, single-phase, 24-pole, 24 circuits, 20 spaces, 120/240V, #4-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR2024B125
UPC	Product Length/Depth
786676444453	3.88 in
Product Height	Product Width
16.75 in	14.31 in
Product Weight	Warranty
24 lb	10 year

Certifications

UL 67

UL 50

Product specifications

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number of spaces

20

Phase

Single-phase

Wire size

#4-2/0 AWG Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

C1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BR2024B125

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)