

Specifications



Eaton BR2024L125R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 125 A, C1R, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #6-2/0 AWG Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR2024L125R
UPC	786676447058
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	21 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Has notch for brhdk125 hold-down kit.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	125 A

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
-----------------	--

BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#6-2/0 AWG Cu/Al
BOX SIZE	C1R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR2024L125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

