

Eaton BR2040B200R

Catalog Number: BR2040B200R

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 40-pole, 40 circuits, 20 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 3R enclosure, d1r box size



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR2040B200R
UPC	Product Length/Depth
786676445757	3.88 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
35.13 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

20

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR2040B200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)