



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR20ITR T-Res Com B+S 20A 125V RCPT

Hubbell Wiring Devices

Catalog Number	BR20ITR
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Weight per unit	0.0460 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	8000
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

Dimensions and Weight

Size	1.32 in x 1.47 in x 3.28 in
------	-----------------------------

Descriptions

Description	T-RES COM B+S 20A 125V RCPT
extra long description	HWK BR20ITR T-RES, COM GRD, 20A 12
Long Description	Straight Blade Devices, Receptacles, Tamper-Resistant Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Product Type	T-Res, Com GRD, 20A 125V, 5-20R, Iv, B+S
Special Features	Tamper Resistant- Self Grounding

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585144153
Manufacturers Part Number	BR20ITR
series	Commercial Specification Grade
UPC	783585144153



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Tamper-Resistant

Packaging

Carton	1
Package	10
Weight Per each	0.046

Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186