



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2448LQN125G

UPC:786676026291

Dimensions:

- Height: 21 IN
- Length: 3.88 IN
- Width: 14.31 IN

Weight:23 LB

Notes:GBK14 installed

Warranties:

- 10 year

Specifications:


- Type: Main lug
- Amperage Rating: 125A
- Box Size: C2
- Bus Material: Aluminum
- Cover: Cover included
- Enclosure: NEMA 1
- Enclosure Material: Metallic
- Interrupt Rating: 10 kAIC
- Mounting: Combination
- Number Of Circuits: 48
- Number Of Spaces: 24
- Number Of Wires: Three-wire
- Phase: Single-phase
- Used With: Type BR 1-inch breakers
- Voltage Rating: 120/240V
- Wire Size: #6-2/0 AWG Cu/Al at 60°C or 75°C

Supporting documents:

- [Eaton Specification Sheet - BR2448LQN125G](#)

Certifications: No Data

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2448LQN125G

UPC:786676026291

Dimensions:

- **Height:** 21 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:23 LB

Notes:GBK14 installed

Warranties:

- 10 year

Specifications:

- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** C2
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Mounting:** Combination
- **Number Of Circuits:** 48
- **Number Of Spaces:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-2/0 AWG Cu/Al at 60°C or 75°C

Supporting documents:

- [Eaton Specification Sheet - BR2448LQN125G](#)

Certifications: No Data

Product compliance: No Data



