



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR3030B100 100A 1PH LD-CTR

Eaton Corp

| | |
|------------------|--|
| Catalog Number | BR3030B100 |
| Manufacturer | Eaton Corp |
| Description | BR Style Load Center, 30 Spaces, 30 Circuits, 100 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 29.13 In Overall Height |
| Weight per unit | 29.0 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|-----------------|---|
| amperage rating | 100 WTT |
| dimensions | 98.5520millimetreX36.3474centimetreX53.3400centimetre |
| Phase | 1 PH |

Dimensions and Weight

| | |
|--------|---|
| Height | 78217250534 |
| Length | INCANDESCENT LAMP, REFLECTOR TYPE; INSIDE FROST COLOR; 2.56 INCH OVERALL LENGTH; INDOOR SPOTLIGHT APPLICATION; 120 V VOLTAGE RATING; 120 STANDARD PACKAGE; 25 W WATTAGE; E17 INTERMEDIATE SCREW BASE TYPE; 1500 LIFE IN HOUR; R14 SHAPE DESIGNATION |
| Width | 14.31 in |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 100A 1PH LD-CTR |
| extra long description | ETN BR3030B100 Type BR 1-inch Loadc |

Manufacturer Information

| | |
|-----------|----------------|
| GTIN | 00786685674742 |
| sub brand | None IN |
| UPC | 786685674742 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | LOADCENTERS & COVERS |
| igcc | 4897 |
| Type | 1-inch loadcenter |
| unspsc code | 39121603 |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 29 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-----------|-------------|
| Enclosure | NEMA 1 |
| Mounting | Combination |
| standard | UL 67;UL 50 |