

Eaton BR3040B200R

Catalog Number: BR3040B200R

Value pack, Main circuit breaker loadcenter, 200A, C3, Aluminum, Interlock cover, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR3040B200R
UPC	Product Length/Depth
786676446051	5.19 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
43 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Value pack

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Interlock cover

Main circuit breaker

BR

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

C3

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR3040B200R

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia