



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR3040L200G**

**UPC:**786676003506

**Dimensions:**

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

**Weight:**28.4 LB

**Notes:**Has notch for brhdk125 hold-down kit.

**Warranties:**

- 10 year

**Specifications:**

- **Special Features:** Ground bar
- **Type:** Main lug
- **Amperage Rating:** 200A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #1 AWG-300 kcmil Cu/Al

**Supporting documents:**

- [Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3040L200G](#)

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR3040L200G**

**UPC:**786676003506

**Dimensions:**

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

**Weight:**28.4 LB

**Notes:**Has notch for brhdk125 hold-down kit.

**Warranties:**

- 10 year

**Specifications:**

- **Special Features:** Ground bar
- **Type:** Main lug
- **Amperage Rating:** 200A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #1 AWG-300 kcmil Cu/Al

**Supporting documents:**

- [Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3040L200G](#)

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data