

Specifications



Eaton BR3060BQN150

BR loadcenter, 150A CSR
MAIN BREAKER, 30
SPACES/60 CIRCUITS,
120/240V, ALUMINUM
BUS, G1 INDOOR BOX
SIZE, #2-300MCM
INCOMING LUG SIZE,
QUICK CONNECT
NEUTRAL
CONFIGURATION

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3060BQN150
UPC	786676026277
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	34 lb
WARRANTY	10 year

Product specifications

SPECIAL FEATURES	QUICK CONNECT NEUTRALS
TYPE	Main circuit breaker
AMPERAGE RATING	150 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	G1
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

EATON

Powering Business Worldwide

Specifications



Eaton BR3060BQN150

BR loadcenter, 150A CSR
MAIN BREAKER, 30
SPACES/60 CIRCUITS,
120/240V, ALUMINUM
BUS, G1 INDOOR BOX
SIZE, #2-300MCM
INCOMING LUG SIZE,
QUICK CONNECT
NEUTRAL
CONFIGURATION

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3060BQN150
UPC	786676026277
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	34 lb
WARRANTY	10 year

Product specifications

SPECIAL FEATURES	QUICK CONNECT NEUTRALS
TYPE	Main circuit breaker
AMPERAGE RATING	150 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	G1
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3



Powering Business Worldwide