



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR4040B200 40C 200A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR4040B200
Manufacturer	Eaton Corp
Description	BR Style Load Center, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 39 In Overall Height
Weight per unit	39.4 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

amperage rating	59120
Box Size	PCA18-1
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX99.0600centimetre
main circuit breaker	CSR
max amps	200
max spaces/poles	40
number of spaces	40 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

### Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

### Dimensions and Weight

Size	L1
------	----

### Descriptions

Description	40C 200A 1PH MB LOADCENTER
extra long description	ETN BR4040B200 BR style 1-inch load

### Manufacturer Information

GTIN	00786676446150
UPC	786676446150



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

## Packaging

Carton	1
Weight Per each	39.36

## Uses, Certifications, and Standards

Enclosure	NEMA 1
standard	UL 67;UL 50