

Eaton BR4242PV200R

Catalog Number: BR4242PV200R

Eaton BR solar-ready loadcenter, Type BR loadcenter, L2R, Copper, 225, Ampere, Cover included, NEMA 3R, 70 max PV, 35 kAIC, 200 A type CSR, 42 Circuits, 42 Spaces



General specifications

Product Name

Eaton BR solar-ready loadcenter

Catalog Number

BR4242PV200R

UPC

786685708270

Product Length/Depth

5.19 in

Product Height

45 in

Product Width

14.31 in

Product Weight

30 lb

Warranty

10 year limited

Compliances

NEC Compliant

Catalog Notes

Rainproof panels are furnished with hub closure plates. Type CSR main breaker factory installed.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type BR loadcenter

Bus material

Copper

Bus Rating

225 A

Cover

Cover included

Main circuit breaker

200A type CSR

Number of circuits

42

Number of spaces

42

Box size

L2R

Enclosure

NEMA 3R

Input

70 max PV

Interrupt rating

35 kAIC

Resources

Brochures

Solar power centers

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 15—Solar Inverters and Electrical Balance of System

Specifications and datasheets

Eaton Specification Sheet - BR4242PV200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia