

# Eaton BR612L125FGP

Catalog Number: BR612L125FGP

Eaton Eaton BR main lug loadcenter, Ground bar, 125 A, 7, Aluminum, Cover not included, NEMA 1, Metallic, 10 kAIC, BR, Flush, NEMA 1, 12 Circuits, Twenty-four pole, 6 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #14-1 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR612L125FGP
<b>UPC</b>	<b>Product Length/Depth</b>
786676002042	3.56 in
<b>Product Height</b>	<b>Product Width</b>
13 in	11 in
<b>Product Weight</b>	<b>Warranty</b>
12.3 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

Ground bar, current design

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover not included

### Main circuit breaker

BR

### Mounting

Flush

### Number of circuits

12

### Number of spaces

6

### Phase

Single-phase

### Voltage rating

120/240V

### Wire size

#14-1 AWG Cu/Al

### Box size

7

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR612L125FGP



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)