

Eaton BRH2100

Catalog Number: BRH2100

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 100 A, 22 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-1/0 AWG Cu/Al, BRH, Type BR Loadcenters



General specifications

Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BRH2100

UPC

786676373906

Product Length/Depth

2 in

Product Height

2.5 in

Product Width

2.9 in

Product Weight

0.7 lb

Compliances

Federal Specifications Classification W-C376

Certifications

UL 490

Catalog Notes

10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

100 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

22 kAIC

Main circuit breaker

BRH

Wire size

#4-1/0 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRH2100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)