

# Eaton BRHX2100

Catalog Number: BRHX2100

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,100 A,22kAIC,Two-pole,120/240V,BRHX,Non-interchangeable,100,Plug-on,BRHX



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BRHX2100
	UPC
	786689041656
<b>Product Length/Depth</b>	<b>Product Height</b>
1.9 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
2.6 in	0.75 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	Contact Manufacturer

**Type**

Quicklag Type BRHX circuit breaker

**Amperage Rating**

100

**Voltage rating**

120/240 V

**Trip Type**

Non-interchangeable

**Circuit breaker type**

BR

**Mounting Method**

Plug-on

**Interrupt rating**

22 kAIC

**Main circuit breaker**

BR

**Connection**

Plug-on

**Number of poles**

Two-pole

**Trip rating**

100

**Brochures**

[Loadcenters and Circuit Breakers](#)

**Specifications and datasheets**

[Eaton Specification Sheet - BRHX2100](#)

**Warranty guides**

[Eaton type BR circuit breaker limited warranty June 2024](#)