

# Specifications



Photo is representative



## Eaton BRHX2110

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 110 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 110, Plug-on, BRHX

### General specifications

<b>PRODUCT NAME</b>	Eaton BR thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	BRHX2110
<b>UPC</b>	786689041663
<b>PRODUCT LENGTH/DEPTH</b>	2.6 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	1.9 in
<b>PRODUCT WEIGHT</b>	0.75 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	Contact Manufacturer



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Quicklag Type BRHX circuit breaker
<b>AMPERAGE RATING</b>	110
<b>VOLTAGE RATING</b>	120/240 V
<b>TRIP TYPE</b>	Non-interchangeable
<b>CIRCUIT BREAKER TYPE</b>	BR
<b>MOUNTING METHOD</b>	Plug-on
<b>INTERRUPT RATING</b>	22 kAIC
<b>MAIN CIRCUIT BREAKER</b>	BR
<b>CONNECTION</b>	Plug-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TRIP RATING</b>	110 A

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRHX2110](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

