

# Eaton BRN130GF

Catalog Number: BRN130GF

Eaton BR GFCI circuit breaker, Plug-in ground fault circuit breaker, 30 A, 10 kAIC, Single-pole, 120/240 V, BRN, Trip-to-center, Plug-on, #14-8 AWG, Ground fault circuit interrupter, GFI, 5 mA



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	BRN130GF
<b>UPC</b>	<b>Product Length/Depth</b>
786689031435	4 in
<b>Product Height</b>	<b>Product Width</b>
1 in	3.4 in
<b>Product Weight</b>	<b>Certifications</b>
0.45 lb	Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Type

Plug-in ground fault circuit breaker

### Amperage Rating

30 A

### Voltage rating

120/240 V

### Trip Type

Trip-to-center

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Protection

5 mA

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BRN

### Connection

Plug-on

### Wire size

#14-8 AWG

### Number of poles

Single-pole

### Trip rating

30 A

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRN130GF](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRN130GF

Catalog Number: BRN130GF

Eaton BR GFCI circuit breaker, Plug-in ground fault circuit breaker, 30 A, 10 kAIC, Single-pole, 120/240 V, BRN, Trip-to-center, Plug-on, #14-8 AWG, Ground fault circuit interrupter, GFI, 5 mA



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	BRN130GF
<b>UPC</b>	<b>Product Length/Depth</b>
786689031435	4 in
<b>Product Height</b>	<b>Product Width</b>
1 in	3.4 in
<b>Product Weight</b>	<b>Certifications</b>
0.45 lb	Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Type

Plug-in ground fault circuit breaker

### Amperage Rating

30 A

### Voltage rating

120/240 V

### Trip Type

Trip-to-center

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Protection

5 mA

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BRN

### Connection

Plug-on

### Wire size

#14-8 AWG

### Number of poles

Single-pole

### Trip rating

30 A

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRN130GF](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)