

Specifications



Photo is representative

Eaton BRP08B150RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 150A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 16 circuits, Single pole, 8 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch brea

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP08B150RF
UPC	786689059095
PRODUCT LENGTH/DEPTH	25 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	18 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

SPECIAL FEATURES

Feed through lugs

Resources

TYPE	Plug-on neutral main circuit breaker loadcenter
AMPERAGE RATING	150 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	16
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	8
PHASE	Single-phase
ACCESSORIES	Feed-through lugs
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3
NEMA RATING	NEMA 3R

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP08B150RF](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

