

# Eaton BRP08E200RF

Catalog Number: BRP08E200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V

## General specifications



Photo is representative

### Product Name

Eaton BR convertible loadcenter

### Catalog Number

BRP08E200RF

### UPC

786689059804

### Product Length/Depth

5.19 in

### Product Height

5.7 in

### Product Width

14.31 in

### Product Weight

18 lb

### Warranty

10 year

### Certifications

UL 67

UL 50

### Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## defaultTaxonomyAttributeLabel

### Special features

Feed-through lug

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Number of circuits

16

### Number of spaces

8

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#1 AWG-300 kcmil

### Box size

X2

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP08E200RF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)