

# Eaton BRP12L125

Catalog Number: BRP12L125

Eaton Eaton BR main lug loadcenter,Indoor,Main lug only,125 A,X0,Aluminum, NEMA 1,Metallic,10kAIC,Surface,flush,24 Circuits,Twenty-four pole,12 Spaces,Two hots,a neutral,and a ground,Single-phase,120/240V,#6-2/0 AWG Cu/Al



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP12L125
UPC	Product Length/Depth
786689052959	16.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
16.1 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Mounting

Surface, flush

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#6-2/0 AWG Cu/Al

### Box size

X0

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### NEMA rating

NEMA 1

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP12L125](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)