

Eaton BRP12N125G

Catalog Number: BRP12N125G

Eaton BR convertible loadcenter, Ground bar, Plug-on neutral main circuit breaker loadcenter, 125A, X1, Aluminum, Cover included, NEMA 1, Metallic, 25kAIC, BR, 24 circuits, 1P, 12 spaces, 2 hots, neutral and ground, Single-phase, #6-1/0AWG Cu/Al, 25, KA



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP12N125G
UPC	Product Length/Depth
786689054953	18.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
17 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Ground bar

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/Al

Accessories

ground bar

Bus Rating

25 kA

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12N125G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Box size

X1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)