

Eaton BRP16B100

Catalog Number: BRP16B100

Plug-on neutral main circuit breaker loadcenter, 100A, X2, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR2100, 32 circuits, Single pole, 16 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers, 1



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP16B100
UPC	Product Length/Depth
786689053079	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
19.5 lb	10 year

Certifications

UL 50
UL 67

Product specifications

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2100

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP16B100](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP16B100

Catalog Number: BRP16B100

Plug-on neutral main circuit breaker loadcenter, 100A, X2, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR2100, 32 circuits, Single pole, 16 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers, 1



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP16B100
UPC	Product Length/Depth
786689053079	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
19.5 lb	10 year

Certifications

UL 50
UL 67

Product specifications

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2100

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP16B100](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia