

# Eaton BRP16L125G

Catalog Number: BRP16L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X1, Aluminum, Gray, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, NEMA 1, 32 Circuits, Twenty-four pole, 16 Spaces, Two hots, a neutral, and a ground, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP16L125G
<b>UPC</b>	<b>Product Length/Depth</b>
786689053123	18.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
18.8 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2125

### Mounting

Surface, flush

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X1

### Color

Gray

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP16L125G](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP16L125G

Catalog Number: BRP16L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X1, Aluminum, Gray, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, NEMA 1, 32 Circuits, Twenty-four pole, 16 Spaces, Two hots, a neutral, and a ground, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP16L125G
<b>UPC</b>	<b>Product Length/Depth</b>
786689053123	18.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
18.8 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2125

### Mounting

Surface, flush

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X1

### Color

Gray

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP16L125G](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)