

# Specifications



Photo is representative



## Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BRP16L125R
<b>UPC</b>	786689059200
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	18.75 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50



Powering Business Worldwide

## Product specifications

TYPE	MLO
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X1
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 3R
NUMBER OF WIRES	3

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP16L125R](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BRP16L125R
<b>UPC</b>	786689059200
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	18.75 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50



Powering Business Worldwide

## Product specifications

TYPE	MLO
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X1
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 3R
NUMBER OF WIRES	3

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP16L125R</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

