

Eaton BRP16L125R

Catalog Number: BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP16L125R
UPC	Product Length/Depth
786689059200	3.88 in
Product Height	Product Width
18.75 in	14.31 in
Product Weight	Warranty
15 lb	10 year

Certifications

UL 67
UL 50

defaultTaxonomyAttributeLabel

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP16L125R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia