

# Specifications



## Eaton BRP16N200

Eaton BR convertible  
loadcenter, Convertible, 200  
A, X4, Aluminum, Cover included, NEMA  
1, Metallic, 10 kAIC, CSR, Combination, 32  
Circuits, Single-pole, 16 Spaces, Two hots, a  
neutral, and a ground, Single-phase, Type BR  
1-inch breakers, 120/240 V

### General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP16N200
UPC	786689053147
PRODUCT LENGTH/DEPTH	27 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Powering Business Worldwide

Product specifications		Resources	
TYPE	Convertible	SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP16N200</a>
AMPERAGE RATING	200 A		
BUS MATERIAL	Aluminum	WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>
COVER	Cover included		
MAIN CIRCUIT BREAKER	CSR		
MOUNTING	Combination		
NUMBER OF CIRCUITS	32		
NUMBER OF POLES	Single-pole		
NUMBER OF SPACES	16		
PHASE	Single-phase		
USED WITH	Type BR 1-inch breakers		
VOLTAGE RATING	120/240 V		
BOX SIZE	X4		
ENCLOSURE	NEMA 1		
ENCLOSURE MATERIAL	Metallic		
INTERRUPT RATING	10 kAIC		
NUMBER OF WIRES	Two hots, neutral and ground		

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE: