

Specifications



Eaton BRP16N200

Eaton BR convertible loadcenter,Convertible,200 A,X4,Aluminum,Cover included,NEMA 1,Metallic,10 kAIC,CSR,Combination,32 Circuits,Single-pole,16 Spaces,Two hots, a neutral, and a ground,Single-phase,Type BR 1-inch breakers,120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP16N200
UPC	786689053147
PRODUCT LENGTH/DEPTH	27 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
PRODUCT TYPE	Convertible loadcenter

Product specifications

TYPE	Convertible
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
MOUNTING	Combination
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	Two hots, neutral and ground

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP16N200](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE: