

Eaton BRP20B100R

Catalog Number: BRP20B100R

Eaton Plug-on neutral main circuit breaker loadcenter, 100A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Single pole, 20 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP20B100R
UPC	Product Length/Depth
786689059231	23 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
26.2 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20B100R](#)

NEMA rating
NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP20B100R

Catalog Number: BRP20B100R

Eaton Plug-on neutral main circuit breaker loadcenter, 100A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Single pole, 20 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP20B100R
UPC	Product Length/Depth
786689059231	23 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
26.2 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20B100R](#)

NEMA rating
NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia