

# Specifications



## Eaton BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BRP20L150
<b>UPC</b>	786689053246
<b>PRODUCT LENGTH/DEPTH</b>	23 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	21 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67



*Powering Business Worldwide*

## Product specifications

TYPE	MLO
AMPERAGE RATING	150 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR2125
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X3
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 1
NUMBER OF WIRES	Two hots, neutral and ground

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP20L150</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BRP20L150
<b>UPC</b>	786689053246
<b>PRODUCT LENGTH/DEPTH</b>	23 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	21 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67



*Powering Business Worldwide*

## Product specifications

TYPE	MLO
AMPERAGE RATING	150 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR2125
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X3
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 1
NUMBER OF WIRES	Two hots, neutral and ground

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRP20L150</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

