

Eaton BRP20L150

Catalog Number: BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1-300 kcmil



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP20L150
UPC	Product Length/Depth
786689053246	23 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
21 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Type

MLO

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2125

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X3

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP20L150](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)