Specifications



Photo is representative





Eaton BRP20N125R

Eaton BR convertible loadcenter, Converible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Threewire, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications	
PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP20N125R
UPC	786689059316
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	18 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Product specifications	
ТҮРЕ	Converible
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Combination
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP20N125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House

30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







