

Eaton BRP30B200G

Catalog Number: BRP30B200G

Plug-on neutral main circuit breaker loadcenter,200A,X6,Aluminum,Cover included,NEMA 1,Metallic,25 kAIC,CSR2200,60 circuits,Single pole,30 spaces,Two hots, a neutral, and a ground,Single-phase,Combination,Type BR 1-inch breakers,120/240V



General specifications

| | |
|----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main breaker loadcenter | BRP30B200G |
| UPC | Product Length/Depth |
| 786689052812 | 34.12 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 31.2 lb | 10 year |
| Certifications | |
| UL 50 | |
| UL 67 | |

Product specifications

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30B200G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP30B200G

Catalog Number: BRP30B200G

Plug-on neutral main circuit breaker loadcenter,200A,X6,Aluminum,Cover included,NEMA 1,Metallic,25 kAIC,CSR2200,60 circuits,Single pole,30 spaces,Two hots, a neutral, and a ground,Single-phase,Combination,Type BR 1-inch breakers,120/240V



General specifications

| | |
|----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main breaker loadcenter | BRP30B200G |
| UPC | Product Length/Depth |
| 786689052812 | 34.12 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 31.2 lb | 10 year |
| Certifications | |
| UL 50 | |
| UL 67 | |

Product specifications

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30B200G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)